

Rittal – The System.

Faster – better – everywhere.



RX 9360.612

RiLineX CB component adaptor

State: 22/05/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.612 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

| | |
|--------------------------------------|---|
| Model No. | RX 9360.612 |
| Design | universal |
| Benefits | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 RAL 35745 |
| Supply includes | 3 connection space covers |
| IP protection category to IEC 60 529 | IP 2XB |
| Rated impulse withstand voltage Uimp | 8 kV |

Features

| | |
|-----------------------------------|---|
| Rated voltage | 690 V AC 600 V AC (UL) |
| Rated insulation voltage U_i | 1,000 V |
| Contamination level | 3 |
| Number of poles | 3-pole |
| Cable outlet | Bottom |
| Cross-section | 15 mm ² 6 mm ² |
| To fit manufacturer (model) | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| To fit busbar system | RiLineX RiLine60 |
| Fundamental frequency | 50...60 Hz |
| Ambient humidity (non-condensing) | 10...90 % |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Operating temperature range | -25 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Dimensions | Width: 108.7 mm Height: 251.4 mm Depth: 62.8 mm |
| Packs of | 1 pc(s). |
| Net weight | 1.472 kg |
| Gross weight | 1.474 kg |
| Copper weight (kg per piece) | 0.608 |
| PCF per pack (cradle-to-gate) | 9.96 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |

Features

| | |
|---------------------|--|
| Product description | RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom. |
|---------------------|--|

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |

Tender text

RiLineX CB component adaptor (Universal Fix)

RiLineX CB component adaptor
for 60 mm busbar systems.

Fastening is carried out using u-nuts in
the two adjustable support rails.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 250 A

Connection: 90 mm²

Cable outlet: bottom

Dimensions: 108 mm x 251 mm x 51 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360612