


Rittal – The System.

Faster – better – everywhere.



RX 9360.730

RiLineX component adaptor

State: 25/01/2026 (Source: rittal.com/au-en)

RX 9360.730 - RiLineX component adaptor

RiLineX component adaptor (32 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



Features

Model No.	RX 9360.730
Design	With connection cable
Benefits	<p>For mounting equipment for top hat rail installation, e.g. motor starter</p> <p>Pre-assembled connection cable</p> <p>Simple clip locking for support rails</p> <p>Optional anti-slip guard</p> <p>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</p> <p>Simple assembly</p> <p>Coordinated accessories reduce the number of different items required</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
Colour	<p>RAL 9005</p> <p>RAL 35745</p>
Connection cables (AWG)	AWG 10
Rated current of round conductor	40 A
Rated current of round conductor (UL)	40 A
Cable outlet	Top

Features

For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	160 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	4 pc(s).
Net weight	1.42
Gross weight	1.45
Copper weight (kg per piece)	0.088

Features

Customs tariff number 85369095

EAN 4028177997011

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity