

# Rittal – The System.

Faster – better – everywhere.



## PK 9505.000

# Polycarbonate enclosures PK

State: 28/06/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9505.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Model No.	PK 9505.000
Design	PK enclosure with solid cover
Product description	Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

# Features

---

Dimensions	Width: 94 mm Height: 94 mm Depth: 81 mm
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	6 pc(s).
Net weight	1.32 kg
Gross weight	1.441 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 94x94x81 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover

---

# Approvals

---

Approvals	C-UL DNV UL UL + C-UL (listed)
Explanations	Declaration of conformity

---

# Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure with solid cover without knockouts

Enclosure: Fibreglass-reinforced polycarbonate  
without knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate

all-round foamed-in PU seal  
Cover screws: Polyamide  
Insulating bungs: Polyethylene  
Supply includes: Cover screws  
Insulating bungs for wall mounting screws  
Accessories: Wall mounting bracket  
Protection category to IEC 60 529: IP 66  
Protection category NEMA: NEMA 4X  
Colour: similar to RAL 7035  
Dimensions (W x H x T): 94 x 94 x 81 mm