

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.100

# Circuit-breaker component adaptor

State: 7/06/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.100 - Circuit-breaker component adaptor 3-pole

For mechanical attachment and direct contacting of circuit-breakers on the board.

## Features

Model No.	SV 9635.100
Function principle	For mechanical attachment and direct contacting of circuit-breakers on the board Circuit-breaker is fitted using variably adjustable fixing points (M4)
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Note	Consider the mounting distance of the circuit-breaker when selecting the circuit-breaker component adaptor Depending on the circuit-breaker used, there may be a reduction in output The technical data may vary for UL applications
Rated current max.	160 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Dimensions	Width: 90 mm Height: 160 mm Depth: 45 mm
Distance between fixing points	25 mm
Cable outlet	Top/bottom
To fit manufacturer (model)	ABB (XT1) Allen Bradley (140G-G) Siemens (3VA10, 3VA11, 3VA51)
Packs of	1 pc(s).
Net weight	0.58 kg
Gross weight	0.582 kg

# Features

---

Copper weight (kg per piece)	0.276
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV CB component adaptor 160 A, 690 V (AC), 600 V (DC), 3-pole WH: 90 x 160 mm, mounting distance 25 mm

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK