


Rittal – The System.

Faster – better – everywhere.



SV 9635.415 Motor controller

State: 23/12/2025 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.415 - Motor controller 3-pole

For controlling motors as direct or reversing starters with integral over-ride protection

Features

Model No.	SV 9635.415
Function principle	For controlling motors as direct or reversing starters with integral over-ride protection The hybrid technology used facilitates frequent switching by semi-conductors with zero wear During operation, mechanical contacts ensure a low heat loss Space-saving configuration thanks to the minimal build width
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Power dissipation (max.)	5.5 W
Safety Integrity Level (SIL) IEC 61508 - Motor protection	2
Safety Integrity Level (SIL) IEC 61508 - safe shutdown	3
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz
Rated current max.	3 A
Note	The technical data may vary for UL applications
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm
Connection of round conductors	0.14 - 2.5 mm ²
Adjustable current monitoring	0.18 - 3 A
Packs of	1 pc(s).
Customs tariff number	85371091
EAN	4028177951860

Features

ETIM 9	EC002572
--------	----------

ECLASS 8.0	27370804
------------	----------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Explanations	Declaration of conformity
--------------	---------------------------