

# Rittal – The System.

Faster – better – everywhere.



## SV 9635.700

## NH fuse-switch disconnector

State: 13/01/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.700 - NH fuse-switch disconnector Size 000

For RiLine Compact busbar system.



## Features

Model No.	SV 9635.700
Function principle	To protect connected equipment Integral test holes provide measurement access to the contact parts of the fuse inserts For cable outlet at the top, the NH fuse-switch disconnector must be mounted on the board rotated through 180°
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Colour	RAL 7035
Test specification	IEC/DIN EN 60 947-3
For NH size	000
Rated operating current max.	125 A
Rated operating voltage	440 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Cable outlet	Top/bottom
Type of electrical connection	Box terminal

# Features

---

Connection of round conductors 2.5 - 50 mm<sup>2</sup>

---

Clamping area for laminated copper bars (W x H) 10 x 10 mm

---

Dimensions  
Width: 49.5 mm  
Height: 174.5 mm  
Depth: 96 mm

---

Packs of 1 pc(s).

---

Net weight 0.52

---

Gross weight 0.562

---

Copper weight (kg per piece) 0.145

---

Customs tariff number 85369095

---

EAN 4028177937604

---

ETIM 9 EC001040

---

ECLASS 8.0 27371401