

# Rittal – The System.

Faster – better – everywhere.



## SR 2323.235

## Swing frame, large, with trim panel

State: 27.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SR 2323.235 - Swing frame, large, with trim panel for TS, VX SE 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel, for mounting 482.6 mm (19") equipment.



## Features

|                      |  |
|----------------------|--|
| Model No.            | SR 2323.235  |
| Design               | 482.6 mm (19") level, side   |
| Product description  | For mounting 482.6 mm (19") equipment.   |
| Material             | Sheet steel  |
| Surface finish       | Frame: Zinc-plated<br>Trim panel: Spray-finished   |
| Colour               | RAL 7035   |
| Supply includes      | Locking rod system with double-bit lock insert<br>Material for attaching   |
| Installation options | In the TS/SE with 130° or 180° opening angle, depending on the chosen mounting kit                                   |
| Assembly instruction | Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required |

# Features

|                       |  |
|-----------------------|--|
| Note                  | For further installation options, see "Technical details"<br>For two-door enclosures TS, SE with a height of 1800 or 2200 mm the next-smallest swing frame must be installed, due to collision with the lock |
| To fit                | Enclosure type: TS<br>VX SE<br>Width: = 800 mm<br>Height: ≥ 1,200 mm   |
| Units                 | 22 U   |
| To fit enclosure type | TS<br>VX SE  |
| Packs of              | 1 pc(s).   |
| Net weight            | 12,888 kg  |
| Gross weight          | 13,566 kg  |
| Customs tariff number | 94039910   |
| ETIM 9                | EC002620   |
| ETIM 8                | EC002620   |
| ECLASS 8.0            | 27189261   |
| Product description   | SR Swing frame, large, with trim panel, for TS, VX SE, for W: 800 mm, 22 U, installed at the side  |

# Tender text

Large swing frame for network enclosure

Large swing frame for network enclosure

22 U can be used for accommodating 482.6 mm (19") equipment.

Torsionally stiff frame, welded from rectangular tube and triple folded support section. Load capacity up to 1500 N when standard hinges are used. Distance from inside edge of door to front edge of swing frame 100 mm, may be installed deeper on a pitch pattern of 25 mm. The swing frame must be fitted to the left / to the right depending on the installation depth of the equipment. Installation position of equipment mounted to the side.

Material: sheet steel

Surface finish: RAL 7035

for enclosure width: W: 800 mm