

# Rittal – The System.

Faster – better – everywhere.



## SZ 2411.841

### Cable gland, brass

State: 05.09.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.841 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SZ 2411.841  |
| Benefits                            | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage.<br>Clamping membranes for even tightening and strain relief to protect the cables |
| Material                            | Brass<br>Seal: CR/NBR  |
| Surface finish                      | Nickel-plated  |
| IP protection category to IEC 60529 | IP 68 (5 bar, 30 min)  |
| Dimensions                          | Height: 36 mm  |
| Thread                              | M32 x 1.5  |
| Thread length                       | 8 mm   |
| Min. cable diameter                 | 15 mm  |
| Max. cable diameter                 | 21 mm  |
| Operating temperature range         | -40 °C...100 °C  |
| torque                              | 15 Nm  |
| Width across flats                  | 34 mm  |
| Dimensions                          | Thread: M32 x 1.5<br>Thread length: 8 mm   |
| Type rating to UL 50E               | Type 1<br>Type 4<br>Type 4X<br>Type 12<br>Type 13  |
| Packs of                            | 5 pc(s).   |

# Features

|                       |               |
|-----------------------|---------------|
| Net weight            | 0.475         |
| Gross weight          | 0.483         |
| Customs tariff number | 74198090      |
| EAN                   | 4028177810051 |
| ETIM 9                | EC000441      |
| ETIM 8                | EC000441      |
| ECLASS 8.0            | 27149109      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)<br>VDE                                 |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |