
Rittal – The System.

Faster - better - everywhere.





SZ 2843.160 EMC cable glands

State: 22.10.2025 (Source: rittal.com/bg-bg)



SZ 2843.160 - EMC cable glands

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2843.160
Design	Cable glands, metric
Product description	The cable sheathing may optionally be interrupted at the contact point or removed completely inside the enclosure. The cable shielding in the enclosure is retained. The supplied lock nut cuts automatically into the paint when screwed onto spray-finished enclosure surfaces, thus creating a conductive connection.
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Note	Minimum shield diameter = cable diameter less cable sheathing
Min. cable diameter	4,5 mm
Max. cable diameter	10 mm
Protection category IP69K	IP 69K
IP protection category to IEC 60 529	IP 68
Shield diameter (min.)	3 mm
Type rating to UL 50E	Type 4X
Packs of	5 pc(s).
Net weight	0.15
Gross weight	0.157
Customs tariff number	74198090
EAN	4028177232808
E-Number Sweden	E1703716

© Rittal 2025

Features

ETIM 9	EC000441	
ETIM 8	EC000441	
ECLASS 8.0	27149109	

Approvals

Approvals	UR + C-UR (recognized) VDE
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3