

**Rittal – The System.**

Faster – better – everywhere.



**SK 3114.200**

**Digital enclosure internal  
temperature display and thermostat**

State: 06.03.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SK 3114.200 - Digital enclosure internal temperature display and thermostat

For installation in the enclosure door or wall.

## Features

Model No.	SK 3114.200
Product description	For installation in the enclosure door or wall.
Technical specifications	Three-digit, 7-segment display Option of switching between °C/°F Includes 1800 mm long NTC sensor Two relay outputs as change-over contact and normally open contact (max. contact load 230 V, 6 A) Freely selectable switching difference
Colour	RAL 7035
Packs of	1 pc(s).
Operating temperature range	0 °C...50 °C
Setting range	5 °C...55 °C
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz 24 V - 60 V (DC)
Storage temperature range	-20 °C...70 °C
IP protection category to IEC 60529	IP 54
Net weight	0,258 kg
Gross weight	0,259 kg
Customs tariff number	90321020
ETIM 9	EC004587
ETIM 8	EC004587
ECLASS 8.0	27210707

# Features

---

Product description	SK Digital enclosure internal , temperature display and thermostat, 100-230 V, 1~, 50/60 Hz, 24-60 V (DC), Installation depth: 100 mm
---------------------	---

# Approvals

---

Approvals	UR
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK