

Rittal – The System.

Faster – better – everywhere.



SK 3120.200 Speed control

State: 12.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3120.200 - Speed control for filter fans and air/air heat exchangers

Temperature-dependent speed control to minimise noise and save energy in part-load operation.

Features

| | |
|--------------------------|--|
| Model No. | SK 3120.200 |
| Product description | Temperature-dependent speed control to minimise noise and save energy in part-load operation. |
| Technical specifications | For mounting on a 35 mm support rail EN 50 022 Phase cross-over with microcontroller Maximum fan output 300 W or 2 A |
| Supply includes | Speed control NTC sensor, length 1.80 m |
| Packs of | 1 pc(s). |
| Speed | 100 % |
| Note | Only suitable for use with single-phase AC motors and equipment Not suitable for EC motors |
| Dimensions | Width: 105 mm Height: 90.5 mm Depth: 60.2 mm |
| Setting range | 20 °C...55 °C |
| Rated operating voltage | 100 V - 230 V |
| Net weight | 0,359 kg |
| Gross weight | 0,39 kg |
| Customs tariff number | 90321020 |
| ETIM 9 | EC000256 |
| ETIM 8 | EC000256 |
| ECLASS 8.0 | 27142320 |

Features

| | |
|---------------------|--|
| Product description | SK speed control unit , for filter fans and Air/air heat exchanger, 100 - 230 V, WHD: 105 x 90.5 x 60.2 mm |
|---------------------|--|

Approvals

| | |
|-----------|----|
| Approvals | UR |
|-----------|----|

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|