

# Rittal – The System.

Faster – better – everywhere.



## SK 3303.130

## Wall-mounted cooling units

State: 21.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3303.130 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.



## Features

Model No.	SK 3303.130
Material	Sheet steel
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 500 W Cooling output L35 L35/60 Hz: 610 W Cooling output L35 L50/50 Hz: 280 W Cooling output L35 L50/60 Hz: 310 W
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 2.6 A At 60 Hz: 2.6 A
Start-up current max.	At 50 Hz: 5.1 A At 60 Hz: 6.4 A
Air throughput (unimpeded air flow)	External circuit: 345 m <sup>3</sup> /h Internal circuit: 310 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.4
Design	wall-mounted

# Features

Dimensions	Width: 280 mm Height: 550 mm Depth: 210 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.17 kg Global Warming Potential (GWP): 1,430 CO2 equivalent (CO2e): 0.24 t
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 360 W Power consumption L35 L35/60 Hz: 380 W Power consumption L35 L50/50 Hz: 465 W Power consumption L35 L50/60 Hz: 490 W
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packs of	1 pc(s).
Customs tariff number	84158200
ECLASS 8.0	27180704

# Approvals

Certificates	Ex
Explanations	Declaration of conformity Declaration of conformity UK