

Rittal – The System.

Faster – better – everywhere.



SK 3335.960 VX25 TopTherm chiller

State: 13.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3335.960 - VX25 TopTherm chiller 8 - 20 kW

VX25 TopThem chillers are compact in design yet have a wide range of cooling applications. They fit perfectly with all enclosures, have a minimum footprint, promise increased efficiency and are instantly available from stock.



Features

| | |
|--|--|
| Model No. | SK 3335.960 |
| Product description | VX25 TopTherm chillers are compact in design and cover a diversity of applications. They integrate perfectly with the enclosure – as series products promising a minimised footprint, increased efficiency and fast availability. |
| Benefits | A single housing size for four output categories Carbon footprint is reduced by up to 35% Reduced volume of refrigerant, thanks to microchannel technology Remote monitoring pre-integrated into the base unit Integrated safety functions create enhanced safety Minimum footprint Convenient servicing |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Fully wired unit ready for connection with side panels and door |
| Protection category to IEC 60 529 | IP 44 (electrics) |
| Total cooling output to DIN EN 14511 Tw18 / Tu35 | Cooling output Tw18 Tu35/50 Hz: 19.4 kW Cooling output Tw18 Tu35/60 Hz: 21.2 kW |
| Air throughput (unimpeded air flow) | At 50 Hz: 6,000 m ³ /h At 60 Hz: 7,200 m ³ /h |

Features

| | |
|---|--|
| Rated operating voltage | 400 V, 3~, 50 Hz 460 V, 3~, 60 Hz |
| Dimensions | Width: 808 mm Height: 2,238 mm Depth: 608 mm |
| Note | Regular leak tests are not prescribed by law. |
| Noise level | 75,6 dB(A) |
| Temperature control | e-controller (factory setting +18 °C) |
| Operating temperature range | 10 °C...43 °C |
| Operating temperature range of cooling medium | 10 °C: 25 °C |
| Temperature hysteresis | ± 1 K |
| Refrigerant/cooling medium | Refrigerant: R-513A Quantity: 2.9 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 1.83 t |
| Pump pressure | At 50 Hz: 2.3 bar At 60 Hz: 3.6 bar |
| Power consumption of cooling medium pump 50/60 Hz | 1.35 / 1.93 |
| Volumetric flow (cooling medium) | At 50 Hz: 55 l/min At 60 Hz: 60 l/min |
| Power consumption Pel | At 50 Hz: 9.58 kW At 60 Hz: 11.9 kW |
| Rated current max. | At 50 Hz: 19.1 A At 60 Hz: 19.45 A |
| Energy efficiency ratio (EER) 50 Hz Tw18/Tu35 DIN EN 14511 | 2,5 |
| Water connections | R 1" internal thread |
| Number of cooling circuits | 1 |
| Tank | Material: PP plastic Volume: 75 l |

Features

| | |
|-----------------------|---|
| Operating weight | 380 kg |
| Packs of | 1 pc(s). |
| Net weight | 262,5 kg |
| Gross weight | 298,5 kg |
| Customs tariff number | 84186900 |
| ETIM 9 | EC002516 |
| ETIM 8 | EC002516 |
| ECLASS 8.0 | 27180713 |
| Product description | SK Chiller TopTherm, in a VX25 housing, 19.4/21.2 kW, 400 – 460 V, 3~, 50/60 Hz, WHD: 808 x 2238 x 608 mm |

Approvals

| | |
|--------------|--|
| Explanations | Declaration of conformity |
| | Declaration of conformity - F-gas regulation |