

# Rittal – The System.

Faster – better – everywhere.



## SK 3341.115

## Rack-mounted fans for 482.6 mm (19")

State: 16.09.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3341.115 - Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m<sup>3</sup>/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SK 3341.115  |
| Product description                 | Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. |
| Colour                              | RAL 7035   |
| Supply includes                     | Fully wired unit ready for connection<br>Terminal strip and assembly parts   |
| Air throughput (unimpeded air flow) | 480 m <sup>3</sup> /h  |
| Rated operating voltage             | 115 V, 1~, 50 Hz/60 Hz<br>110 V (DC)   |
| Rated current max.                  | At 50 Hz: 0.69 A<br>At 60 Hz: 0.69 A   |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 6 A  |
| Dimensions                          | Width: 482.6 mm<br>Height: 44 mm<br>Depth: 200 mm  |
| Distance between axes of fans       | 85 mm  |
| No. of fans                         | 3  |
| Noise level                         | At 50 Hz: 52 dB(A)   |
| Operating temperature range         | -10 °C...55 °C   |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 2  |

# Features

|                       |               |
|-----------------------|---------------|
| Gross weight          | 2.74          |
| Customs tariff number | 84145915      |
| EAN                   | 4028177041479 |
| ETIM 9                | EC000320      |
| ETIM 8                | EC000320      |
| ECLASS 8.0            | 27180716      |

# Approvals

|              |                               |
|--------------|-------------------------------|
| Approvals    | UR + C-UR (recognized)<br>VDE |
| Explanations | Declaration of conformity     |