

# Rittal – The System.

Faster – better – everywhere.



## SK 3329.104

# Wall-mounted cooling units

State: 19.07.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3329.104 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SK 3329.104   |
| Supply includes                   | Fully wired ready for connection<br>Drilling template<br>Assembly parts |
| Design                            | wall-mounted  |
| Protection category to IEC 60 529 | External circuit IP 34<br>Internal circuit IP 54                        |
| Refrigerant/cooling medium        | Refrigerant: R134a<br>Quantity: 0 kg                                    |
| Temperature control               | Basic controller (factory setting +35 °C)                               |
| Operating temperature range       | 20 °C...55 °C   |
| Setting range                     | 30 °C...55 °C   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 68.4  |
| Gross weight                      | 72  |
| EAN                               | 4028177389434   |
| ECLASS 8.0                        | 27180704  |

## Approvals

|           |  |
|-----------|--|
| Approvals | UL + C-UL (listed)<br>UR + C-UR (recognized) |
|-----------|--|

# Approvals

|              |   |
|--------------|---|
| Certificates | EAC   |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

## Tender text

Wall-mounted cooling unit Rittal TopTherm PLUS -  
NEMA 4 x, with RiNano coating and  
integral condensate evaporation  
Useful cooling output to DIN 3168 L35 L35 2500/2750 W  
Rated operating voltage 230 V, 1~, 50/60 Hz  
Power consumption Pel to DIN 3168 L35 L35 1450/1675 W  
Dimensions W x H x D [mm] 405 x 1650 x 368  
Refrigerant R 134 a  
Temperature range 20°C to 55°C (Setting range +30°C to +55°C)  
Temperature control and monitoring via  
basic controller with floating fault signal contact  
and connection for door-operated switch  
Factory setting 35°C  
Connection via pluggable terminal strip  
Protection category NEMA 4X  
Weight 83 kg  
Colour RAL 7035