Rittal - The System.

Faster – better – everywhere.





SK 3329.600

TopTherm wall-mounted cooling unit Blue e

State: 15.11.2025 (Source: rittal.com/bg-bg)



SK 3329.600 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".



Features

Model No.	SK 3329.600
Design	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W).
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Stainless steel 1.4301 (AISI 304)
Colour	RAL 9007
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts Integral electric condensate evaporation
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.55 kW Cooling output L35 L35/60 Hz: 2.6 kW Cooling output L35 L50/50 Hz: 1.8 kW Cooling output L35 L50/60 Hz: 1.8 kW

© Rittal 2025 2

Features

Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 7.9 A
	At 60 Hz: 10.1 A
Start-up current max.	At 50 Hz: 25 A
	At 60 Hz: 22 A
Air throughput (unimpeded air	External circuit: 1,230 m³/h
flow)	Internal circuit: 1,230 m³/h
Energy efficiency ratio (EER) 50/60	Refrigeration factor L35 L35 (EER) 50 Hz: 2.11
Hz L35 L35	Refrigeration factor L35 L35 (EER) 60 Hz: 1.7
Design	wall-mounted
Dimensions	Width: 400 mm
	Height: 1,580 mm
	Depth: 295 mm
Protection category to IEC 60 529	External circuit IP 34
	Internal circuit IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A
	Quantity: 1.15 kg
	Global Warming Potential (GWP): 631
	CO2 equivalent (CO2e): 0.73 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C55 °C
Storage temperature range	-40 °C70 °C
Setting range	20 °C55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 1.21 kW
	Power consumption L35 L35/60 Hz: 1.53 kW
	Power consumption L35 L50/50 Hz: 1.41 kW
	Power consumption L35 L50/60 Hz: 1.8 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Miniature circuit-breaker/fuse: 16 A
Note on Model No.	Extended delivery times.

© Rittal 2025 3

Features

Packs of	1 pc(s).
Net weight	65.55
Gross weight	69
Customs tariff number	84158200
EAN	4028177379886
E-Number Sweden	E3404565
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Approvals	UL + C-UL (listed)
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025