## Rittal - The System.

Faster – better – everywhere.





SK 3382.610

# TopTherm Blue e roof-mounted cooling unit

State: 28.11.2025 (Source: rittal.com/bg-bg)



# SK 3382.610 - TopTherm Blue e roof-mounted cooling unit Total cooling output 0.50 - 4.00 kW

Energy-efficient Blue e roof-mounted cooling units in output categories from 500 W to 4,000 W with e-Comfort controller integrated as standard and electrical condensate evaporation.





#### **Features**

Model No.	SK 3382.610
Design	roof-mounted
Product description	Energy-efficient Blue e roof-mounted cooling units with integral e- Comfort controller and electric condensate evaporation as standard.
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Stainless steel 1.4301 (AISI 304)
Colour	RAL 9007
Supply includes	Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts

© Rittal 2025 2

### Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.6 kW Cooling output L35 L35/60 Hz: 0.62 kW Cooling output L35 L50/50 Hz: 0.47 kW Cooling output L35 L50/60 Hz: 0.43 kW
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Note	The roof-mounted cooling unit 3273.500 is also suitable for office applications, thanks to its low noise level.
Rated current max.	At 50 Hz: 5.9 A At 60 Hz: 6.8 A
Start-up current max.	At 50 Hz: 18.2 A At 60 Hz: 15.9 A
Air throughput (unimpeded air flow)	External circuit: 910 m³/h Internal circuit: 440 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.62 Refrigeration factor L35 L35 (EER) 60 Hz: 1.91
Design	roof-mounted
Dimensions	Width: 597 mm Height: 417 mm Depth: 380 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.3 kg Global Warming Potential (GWP): 1,430 CO2 equivalent (CO2e): 0.19 t
Type of electrical connection	Plug-in terminal strip
Duty cycle	100 %
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C55 °C
Storage temperature range	-40 °C70 °C
Setting range	20 °C55 °C

© Rittal 2025 3

#### **Features**

Power consumption Pel	Power consumption L35 L35/50 Hz: 0.37 kW Power consumption L35 L35/60 Hz: 0.34 kW Power consumption L35 L50/50 Hz: 0.41 kW Power consumption L35 L50/60 Hz: 0.39 kW
Permissible operating pressure (p. max.)	28 bar
Note on Model No.	Extended delivery times.
Pre-fuse	Transformer circuit-breaker: 6.310 A
Packs of	1 pc(s).
Net weight	35
Gross weight	35
Customs tariff number	84158200
EAN	4028177380011
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

# **Approvals**

Approvals	C-UR UL + C-UL - FTTA
Certificates	EAC
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025