

Rittal – The System.

Faster – better – everywhere.



SV 3562.000 Plate clamp

State: 13.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3562.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

| | |
|---|--|
| Model No. | SV 3562.000 |
| Product description | For connecting laminated copper bars, no drilling required. |
| Material | Sheet steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 54 x 10 mm |
| To fit busbars | 50 x 10 |
| To fit busbars | Busbar E-Cu |
| Packs of | 3 pc(s). |
| Net weight | 1,2 kg |
| Gross weight | 1,412 kg |
| PCF per pack (cradle-to-gate) | 5.4 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |
| Product description | SV Plate clamp, for laminated copper bar, clamping area WH: 54x10 mm, for busbar WH: 50x10 mm |

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

SV plate clamps

for E-Cu busbars with 3 - 10 mm thickness.

For bar width: up to 50 mm

Clamping area for laminated copper bars:

54 x 10 mm

Tightening torque:

6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated