


# Rittal – The System.

Faster – better – everywhere.



## SV 3554.000 Plate clamp

State: 14.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3554.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

## Features

Model No.	SV 3554.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	34 x 10 mm
To fit busbars	12 x 5 - 30 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Net weight	0,699 kg
Gross weight	0,8 kg
PCF per pack (cradle-to-gate)	3.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146
Product description	SV Plate clamp, for laminated copper bar, clamping area WH: 34x10 mm, for busbar WH: 12x5-30x10 mm

## Approvals

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK

## Tender text

SV plate clamps

for E-CU busbars with 3 - 10 mm thickness.

For enclosure width: up to 30 mm

Clamping area for laminated copper bars: 34 x 10 mm

Tightening torque

6 - 8 Nm

Material: sheet steel, zinc plated, passivated