

Rittal – The System.

Faster – better – everywhere.



AS 4055.070

**Manual hydraulic punch set, M16 -
M63**

State: 16.09.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.070 - Manual hydraulic punch set, M16 - M63

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

Features

| | |
|--|--|
| Model No. | AS 4055.070 |
| Design | This set includes the standard hole punches M16 to M63 |
| Product description | Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm. |
| Benefits | Extend tool life with a built-in overpressure valve Hole punches, hydraulic punches and accessories for making round, square and rectangular cut-outs in steel steel and stainless steel |
| Supply includes | Manual hydraulic punch, straight 7 splitter hole punches, triple splitting Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 10 mm Spacer sleeve set (3-part) Plastic case |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm |
| Ø punch | 16,2 mm 20,4 mm 25,4 mm 32,5 mm 40,5 mm 50,5 mm 63,5 mm |

Features

| | |
|-----------------------|---|
| For threads | M16 M20 M25 M32 M40 M50 M63 |
| Packs of | 1 pc(s). |
| Net weight | 5.3 |
| Gross weight | 5.34 |
| Customs tariff number | 82034000 |
| EAN | 4028177807945 |
| ETIM 9 | EC002121 |
| ETIM 8 | EC002121 |
| ECLASS 8.0 | 21049046 |