Rittal – The System.

Faster – better – everywhere.





AS 4052.142 Screwdrivers

State: 15.12.2025 (Source: rittal.com/bg-bg)



AS 4052.142 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

Features

| Model No. | AS 4052.142 | |
|-----------------------|---|--|
| Design | Isolation protection 1000 V For plus/minus | |
| Product description | With a long, slender handle and high-performance tip with non-transfer insulation. | |
| Benefits | Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working | |
| Material | Blade: Chrome-molybdenum-vanadium alloy Handle core: Hard plastic Handle body: Elastic, highly flexible plastic | |
| Colour | Handle: Anthracite and Rittal Power Pink | |
| Blade dia. | 6 mm | |
| Blade length | 100 mm | |
| Blade tip | Z 2 | |
| Handle dia. | 27 mm | |
| Handle length | 115 mm | |
| Standards | IEC 60 900 | |
| Packs of | 3 pc(s). | |
| Customs tariff number | 82054000 | |
| EAN | 4028177807303 | |
| ETIM 9 | EC000144 | |
| | | |

© Rittal 2025

Features

| ETIM 8 | EC000144 | |
|------------|----------|--|
| ECLASS 8.0 | 21040406 | |

© Rittal 2025 3