

**Rittal – The System.**

Faster – better – everywhere.



# AS 4055.116

## Splitter hole punch, round

State: 11.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.116 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

## Features

|  |   |
|--|---|
| Model No.  | AS 4055.116   |
| Design   | With triple splitting   |
| Product description                                    | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes  | Female dies<br>Male dies  |
| Machinable material                                    | Stainless steel   |
| Maximum machinable material thickness, stainless steel | 2 mm  |
| Ø punch  | 16,2 mm   |
| For threads  | M16   |
| Note   | When operating with wrenches, tension screws with ball bearings should be used.           |
| Suitable for hydraulic bolt order number               | 4055.665  |
| Tension screw (Ø x L)                                  | 11.1 x 60 mm  |
| Hydraulic tension screw Ø                              | 11,1 mm<br>19 cm  |
| Packs of   | 1 pc(s).  |
| Net weight   | 0,043 kg  |
| Gross weight   | 0,059 kg  |
| Customs tariff number                                  | 82073010  |
| ETIM 9   | EC000156  |

# Features

---

|                     |  |
|---------------------|--|
| ETIM 8              | EC000156   |
| ECLASS 8.0          | 21049047   |
| Product description | Splitter hole punch, round for stainless steel, round, with triple splitting |

---