Rittal – The System.

Faster – better – everywhere.





AS 4055.122 Splitter hole punch, round

State: 29.10.2025 (Source: rittal.com/bg-bg)



AS 4055.122 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.122	
Design	With triple splitting	
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.	
Supply includes	Female dies Male dies	
Machinable material	Stainless steel	
Maximum machinable material thickness, stainless steel	2 mm	
Ø punch	22,5 mm	
Note	When operating with wrenches, tension screws with ball bearings should be used.	
Suitable for hydraulic bolt order number	4055.665	
Tension screw (Ø x L)	11.1 x 60 mm	
Hydraulic tension screw Ø	11,1 mm 19 cm	
Packs of	1 pc(s).	
Net weight	0.093	
Gross weight	0.113	
Customs tariff number	82073010	
EAN	4028177808010	
ETIM 9	EC000156	

© Rittal 2025

Features

ETIM 8	EC000156	
ECLASS 8.0	21049047	

© Rittal 2025 3