

Rittal – The System.

Faster – better – everywhere.



VX 5301.516

Castor module

State: 01.02.2026 (Source: rittal.com/bg-bg)

VX 5301.516 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

Features

Model No.	VX 5301.516
Product description	For mobile use even with preconfigured enclosures. The castor module is screw-fastened to the structure directly underneath the base frame and is suitable for transporting configured enclosures on flat ground and inside buildings.
Supply includes	1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts
Dimensions	Width: 556 mm Height: 79 mm Depth: 203 mm
Assembly instruction	The base area must be open at the mounting points
To fit	Enclosure type: VX: = 600 mm Enclosure type: VX IT
Load capacity	Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N
Note	The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground.
Packs of	1 pc(s).
Net weight	10
Gross weight	10.3
Customs tariff number	83024900
EAN	4028177952492
E-Number Sweden	E7282570
ETIM 9	EC002621
ECLASS 8.0	27189262

Tender text

Castor module for W: 600 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts