Rittal – The System.

Faster – better – everywhere.





AS 4055.563 Splitter hole punch, round

State: 15.11.2025 (Source: rittal.com/bg-bg)



AS 4055.563 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.563
Design	With triple splitting
Product description	
Supply includes	Female dies Male dies
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	63,5 mm
For threads	M63
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	0.931
Gross weight	1.004
Customs tariff number	82073010
EAN	4028177808829

© Rittal 2025

2

Features

ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047

© Rittal 2025 3