### Rittal – The System.

Faster – better – everywhere.





## AS 4055.581 Splitter hole punch set, M12 to M40

State: 17.11.2025 (Source: rittal.com/bg-bg)



# AS 4055.581 - Splitter hole punch set, M12 to M40 for sheet steel, with triple splitting

For punching round cut-outs

#### **Features**

Model No.	AS 4055.581
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	6 female dies
	6 male dies
	Tension screw with ball bearing Ø 6 x 40 mm
	Tension screw with ball bearing Ø 9.5 x 50 mm
	Tension screw with ball bearing Ø 19 x 55 mm
	HSS pilot drill Ø 10 mm
	1 can of lubricant paste
	Plastic case
Machinable material	Sheet steel
Maximum machinable material	1,5 mm
thickness, sheet steel	2 mm
	2 mm
	2 mm
	3 mm
	3 mm
Ø punch	12,5 mm
	16,2 mm
	20,4 mm
	25,4 mm
	25,4 mm 32,5 mm

© Rittal 2025

### **Features**

For threads	M12
	M16
	M20
	M25
	M32
	M40
Note	When operating with wrenches, tension screws with ball bearings
	should be used.
Suitable for hydraulic bolt order	4055.660
number	4055.661
	4055.661
	4055.661
	4055.663
	4055.663
Packs of	1 pc(s).
Net weight	2.2
Gross weight	2.256
Customs tariff number	82073010
EAN	4028177808843
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21044719

© Rittal 2025 3