


# Rittal – The System.

Faster – better – everywhere.



## VX 5301.518 Castor module

State: 04.08.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.518 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

## Features

Model No.	VX 5301.518
Product description	For mobile use even with preconfigured enclosures. The castor module is screw-fastened to the structure directly underneath the base frame and is suitable for transporting configured enclosures on flat ground and inside buildings.
Supply includes	1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts
Dimensions	Width: 756 mm Height: 203 mm Depth: 79 mm
Assembly instruction	The base area must be open at the mounting points
To fit	Enclosure type: VX: = 800 mm Enclosure type: VX IT
Load capacity	Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N
Note	The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground.
Packs of	1 pc(s).
Net weight	11.5
Gross weight	12.12
Customs tariff number	94039910
EAN	4028177952515
E-Number Sweden	E7282571
ETIM 9	EC002621
ECLASS 8.0	27189262

# Tender text

Castor module for W: 800 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts