

Rittal – The System.

Faster – better – everywhere.



DK 5301.612

Sheet steel door, vertically divided, solid

State: 16.08.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5301.612 - Sheet steel door, vertically divided, solid for VX IT

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.



Features

| | |
|----------------------|--|
| Model No. | DK 5301.612 |
| Product description | To replace existing doors. The minimal rotation radius of the individual doors allows the distance between individual bayed enclosure suites to be reduced. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 Comfort handle VX, hinges: RAL 9005 |
| Supply includes | Door, vertically divided, with comfort handle VX for semi-cylinders with security lock 3524 E, right 3 x 180° hinges, fitted on each half of the door Assembly parts |
| Assembly instruction | For a door opening angle of 180° when baying, a 180° baying hinge is required |

Features

| | |
|-------------------------------------|---|
| Note | Door opening angle for stand-alone siting: max. 240° Door opening angle when baying: max. 160° |
| IP protection category to IEC 60529 | IP 20 |
| To fit | Enclosure type: VX IT Width: = 800 mm Height: = 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 43 |
| Gross weight | 49 |
| EAN | 4028177955134 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |