

Rittal – The System.

Faster – better – everywhere.



VX 5332.818

Network/server rack VX IT

State: 23.08.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5332.818 - Network/server rack VX IT with vented door, with 482.6 mm (19") mounting angles Dynamic

VX IT network/server enclosure, vented, for room climate control. 482.6 mm (19") interior installation with depth-variable 482.6 mm (19") mounting angles in the dynamic version, available in a range of size variants.



Features

Model No.	VX 5332.818
Material	Sheet steel Aluminium
Surface finish	Enclosure frame: Powder-coated Interior installation: Spray-finished Rear door and roof: Powder-coated Front door: Aluminium, anodised, sheet steel powder coated
General colour	RAL 7035
Colour	Enclosure frame, rear door and roof: RAL 7035 Front door: Vertical sections, silver coloured and horizontal sections, RAL 9005 Interior installation, vent grille at the front: RAL 9005 Handle and hinges: RAL 9005

Features

Supply includes	<p>VX enclosure frame with doors and roof plate</p> <p>Aluminium/sheet steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges</p> <p>Sheet steel rear door, vented (vented surface area approx. 85% perforated), vertically divided, 180° hinges</p> <p>Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E</p> <p>Mounting angles, 482.6 mm (19")</p> <p>Spacers, height 50 mm, to raise a cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose). Not required for variants without a cut-out.</p> <p>12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose)</p> <p>25 multi-tooth screws, conductive (supplied loose)</p> <p>IPPC pallet</p> <p>Roof plate, multi-piece, with cable entry in the corner sections front and rear</p>
Dimensions	<p>Width: 600 mm</p> <p>Height: 2,450 mm</p> <p>Depth: 1,200 mm</p>
Units	52 U
Units	52 U
Free mounting space to the 482.6 mm (19") level, front/rear	150 mm / 325 mm
Mounting position of the 482.6 mm (19") level	front and rear
Distance between levels as delivered	725 mm
482.6 mm (19") attachment	with mounting bracket screw-fastened to the frame at the top and on depth stays at the bottom
Design	dynamic
Roof design	multi-piece, with cable entry in the corner sections front and rear
Rear door design	Sheet steel door, vented, vertically divided, 180° hinges
Front door design	Aluminium/sheet steel door, vented, one-piece, 180° hinges
Mounting angle design	Dynamic 482.6 mm (19") mounting angles in the VX IT

Features

Base design	Open
482.6 mm (19") level(s) version	482.6 mm (19") level, front and rear
Mounting angles position	482.6 mm (19") level, front and rear
Load capacity	18 000 N
Max. load capacity (static) per enclosure to UL 2416	15 000 N
Note	Depending on how and where it is sited, the door opening angle may vary for selected applications
Basic material	Sheet steel
Packs of	1 pc(s).
PCF per pack (cradle-to-gate)	251.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177945616
ETIM 9	EC002499
ECLASS 8.0	27180207

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK

Tender text

VX IT network, server and electronics enclosure, "dynamic" variant, IT rack, installation height 52 U, vented aluminium sheet steel door at the front,

two-piece, vented sheet steel door at the rear.

Rack frame:

Pre-configured IT rack, comprising a torsionally rigid, welded and full symmetrical frame of rolled, 9-fold closed hollow profile, with punchin in a 25 mm pitch pattern.

Frame with integrated M6 blind rivet nuts, to enable fittings to be mounted without impairing the degree of protection. All profile edges are chamfered. Horizontal sections with integrated channel above the PU foam seal as protection for the seal.

Same profile on all sides, with two mounting levels accessible from inside and outside, for fast and space-saving interior installation.

Square holes on all sides to enable the use of cage nuts and metric screws up to M8.

Base:

Welded base frame with integrated reinforcement to enable direct bolting to the floor from inside the enclosure. Open base frame, without gland plates, for optional individual configuration with base modules from the range of accessories.

Baying possible on all sides. Static load capacity up to 18,000 N, and up to 15,000 N acc. to UL 2416.

Front and rear door:

Vented aluminium sheet steel front door, with perforated sheet steel panel, 85% free ventilation area, held in a frame of aluminium sections vertical sections silver-grey anodised, horizontal sections painted, RA 9005.

Door with three hinges and four-point locking rod. Door hinge can be swapped from right to left, hinge pins with integrated adjustment aid, door opening angle 240° for stand-alone enclosures, 105° with baying.

Sheet steel rear door, two-piece, vertically divided, vented.

Perforated surface with 85% free ventilation area.

Rear door with integrated reinforcement section on both sides, with three hinges and three-point locking rod.

Door hinge can be swapped from right to left, hinge pins with integrated door opening angle 240° for stand-alone enclosures, 160° with baying.

Baying hinges with 180° opening angle for front and rear doors available separately via the range of accessories.

Both doors with comfort handle for semi-cylinder (30/10) mm, with security lock 3524 E.

Roof plate:

Multi-part roof plate with cable entry via brush strips in the front and rear corners on both sides. The multi-part design permits removal of the roof plate with the cabling in place, which greatly simplifies later retrofitting or modification.

Mounting levels:

Enclosure pre-configured with two 482.6 mm (19") mounting levels, front and rear.

The total static load capacity of both mounting levels is 18,000 N.

Dynamic load capacity (moving on transport module) up to 10,000 N.

Mounting level comprising universal mounting angles for server, network and electronics applications, front and rear, depth-variable, 12.5 mm pitch pattern,

screw-fastened to the enclosure frame via mounting brackets at top and depth stays at bottom.

Imperial mounting levels can be positioned either symmetrically or asymmetrically with an offset to each other. Alternative mounting dimensions for 21", 23" or 24" components can also be realised.

Mounting angles front and rear, material thickness 2.5 mm, with additional pitch pattern in accordance with the standard EIA 310 E. All height units are marked on the mounting angles and numbered in opposite directions. Height unit markings on both mounting levels can be read from both inside and outside for simplified component installation.

Front mounting angles prepared for tool-free mounting of cable routing aids and organisation of structured cabling with maximum packing density.

Rear mounting angles prepared on both sides for mounting of a Power Distribution Unit (PDU) in 1 U form factor for electrical power distribution in the enclosure, avoids occupying component installation space thanks to space-saving side mounting in the zero-U space between mounting level and side panel.

Supply includes:

Practice-proven mounting accessories, such as spacers for optional raising of the cover plate, fixing accessories for 19" components comprising twelve 19" fasteners, 1 U, contacting, and 25 hexagon socket screws, conductive, with washers for thread size M5.

Potential equalisation:

All panel parts with automatic potential equalisation or prepared for the attachment of earthing straps.

482.6 mm (19") assembly parts are supplied loose.

A potential equalisation kit is available as an accessory.

Side panels:

Side panels are not included in the scope of supply.

One-part screw-fastened variant (IP 55) as well as horizontally divided variant (IP 20) available via the range of accessories.

QR code:

Printed QR codes on all panel parts, the roof, doors and rating plate provide for the unambiguous marking of individual components, simplify access to relevant product information and documentation, and ensure the full traceability of single parts.

Material:

Enclosure frame, roof: Sheet steel 1.5 mm

Rear door: Sheet steel 1.5 mm

Front door: Aluminium, sheet steel 1.5 mm

482.6 mm (19") mounting angles: Sheet steel 2.5 mm

Surface finish (sheet steel):

Triple surface treatment for corrosion protection and resistance to mineral oils, lubricants, machining emulsions and solvents: Nanoceramic coating, electrophoretic dipcoat priming, textured powder coating in RA 7035/9005.

Protection classes:

Protection category according to IEC 60 529 (with mounted side panels or in a bayed suite with seals):

IP 00

Protection category according to NEMA (with mounted side panels or in a bayed suite with seals):

Surface:

Cabinet frame, rear door and roof: powder coated

Interior: painted

Front door: aluminium, anodised/sheet steel, powder-coated

Approvals:

UL2416 NITW (NFPA70, NFPA75)

IEC/EN 60950 (CB Certificate and Report)

IEC/EN 62368 (CB Certificate and Report)

Dimensions (WHD): 600x2450x1200 mm

Model No: VX IT 5332.818

Manufacturer: Rittal GmbH & Co. KG