


Rittal – The System.

Faster – better – everywhere.



DK 7391.000

Data Rack



State: 01.02.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7391.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation as well as extensive mobility when using twin castors.



Features

Model No.	DK 7391.000
Material	Profile frame, base/plinth: Sheet steel Feet: Die-cast zinc
General colour	RAL 7035
Colour	Profile frame, base/plinth: RAL 7035 Trim panel, feet: RAL 5018
Supply includes	Torsionally stiff profile frame with 482.6 mm (19") punchings Stable base/plinth with integral feet, with the option of floor anchoring without base trim panels Mounting accessories
Dimensions	Width: 550 mm Height: 1,500 mm Depth: 750 mm
Units	31 U
Units	31 U
Distance from the second mounting level, 50 mm pitch pattern	150 - 350 mm

Features

Pitch pattern between the mounting levels	50 mm
Load capacity of the 482.6 mm (19") mounting angles	1500 N
Note	Order second mounting level separately
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	16.781
Gross weight	17.664
PCF per pack (cradle-to-gate)	67.1 kg CO ₂ eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
EAN	4028177129795
E-Number Sweden	E7239646
ETIM 9	EC002507
ECLASS 8.0	27180602

Tender text

482.6 mm (19 inch) rack, 31 U

Torsionally stiff frame section, welded from 2 mm sheet steel, with integral 482.6 mm (19 inch) punchings and round and square holes in the 25 mm DIN pitch pattern for accommodation of cabling systems and 482.6 mm (19 inch) components.

The rack is depth-adjustable in a pitch pattern of 50 mm on a folded sheet steel base/plinth with die-cast zinc feet. The base/plinth can accommodate a second 482.6 mm (19 inch) mounting level, offers the option of floor anchoring and fastening facilities for levelling feet and castors.

Infinitely bayable.

Material: Sheet steel

Colour: RAL 7035

Dimensions: Rack height 1500 mm, 31 U,

base/plinth: WxD: 550 x 750 mm