


Rittal – The System.

Faster – better – everywhere.



CP 6206.460

Tilting adaptor +100°/–60°

State: 08.07.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6206.460 - Tilting adaptor +100°/-60° for support arm connection 120 x 65 mm

For mounting on IW worktop, prepared for attachment Ø 130 mm, surfaces or attachments/ couplings with support arm connection 120 x 65 mm. To fit enclosures up to 20 kg with support arm connection. With cable tube for protected cable entry.

Features

Model No.	CP 6206.460
Design	For mounting on IW worktop, prepared for attachment of 130 mm diameter Surfaces Attachment/coupling with support arm connection 120 x 65 mm To fit enclosures up to 20 kg with support arm connection 90 x 71 mm Ø 130 mm 120 x 65 mm VESA Standard 75 With cable tube for protected cable entry
Product description	Tilting angle adjustable in 7.2° increments via clamping lever and may be limited to +100°/-15° using the stop screw supplied loose.
Material	Tilting adaptor: Sheet steel, spray-finished Concertina section: Plastic
Colour	Tilting adaptor: RAL 7035 Concertina section: RAL 7024
Supply includes	Assembly parts Concertina section
Rotating/tilting	Yes
Tilt angle note	Adjustable in 7.2° increments via clamping lever and may be limited to +100°/-15° using the stop screw supplied loose
Packs of	1 pc(s).
Net weight	0,86 kg
Gross weight	0,871 kg

Features

PCF per pack (cradle-to-gate)	3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC000882
ECLASS 8.0	27400556
Product description	CP Tilting adaptor +100°/-60°, CP 60/120, for support arm connection 120 x 65 mm

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------
