

Rittal – The System.

Faster – better – everywhere.



DK 7856.025 Connection cable

State: 16.04.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7856.025 - Connection cable for PSM rail

Preassembled connection cable for the Power System Module.

Features

Model No.	DK 7856.025
Design	3-phase
Connector (type)	CEE (3P+N+PE)
Rated current (max.)	16 A
Dimensions	Length: 3 m
Sockets	Wago X-Com
Packs of	1 pc(s).
Net weight	0,94 kg
Gross weight	0,96 kg
Customs tariff number	85444290
ETIM 9	EC001576
ECLASS 8.0	27060402
Product description	DK Connection cable, L: 3 m, 16 A, 3-phase, Wago X-Com, CEE, For PSM

Tender text

Power System Module connection cable

Installation via the plug & play system:

The pre-configured connection cable with fitted AC IEC309 plug is used to supply the power system module plus busbar. A 5-pole plug-in connector strip is used to connect up to the busbar.

Another connection cable is required to supply the second redundant power circuit.

Technical specifications:

Three-phase voltage range 110V - 400V AC 50/60 Hz,
neutral line is not needed

Max. current per supply: 3 x 16A

Type of cable: H07RN-F 5G2.5 mm²

Cable length: 3 m

1st cable end: CEE-plug 16A / 400V (IEC309, red)

2nd cable end: Wago plug