

Rittal – The System.

Faster – better – everywhere.



TX 7888.898

Network rack TX CableNet

State: 02.04.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TX 7888.898 - Network rack TX CableNet with glazed door

The TX CableNet – places extra space at your disposal by avoiding the problem of unnecessarily wide or deep IT racks. This IT network rack is thus also suitable for use in smaller IT environments and is already optimally prepared for individual interior installation.



Features

Model No.	TX 7888.898
Design	2nd generation Pre-configured with glazed door with side panels With roof plate
Product description	Optimum IT rack solution for use in tight spaces, in rooms with low ceilings or wherever accessibility is otherwise restricted.No power losses due to unused rack space in case of population with exclusively small electrical components.

Features

Benefits	<p>New roof plate concept: When cabling, the depth is utilised in full, plus optional integration of a fan module</p> <p>Efficient frame concept for individual configuration</p> <p>482.6 mm (19") mounting angles, front and rear, adjustable in the depth</p> <p>Side panels, screw-fastened for rapid access</p> <p>Base/plinth system VX, vented, for simple cable entry via the base area or within a bayed suite, provides additional climate control support.</p> <p>Comprehensive range of accessories for bespoke interior configuration</p>
Material	<p>Enclosure: Sheet steel</p> <p>Door: Sheet steel, 1.2 mm</p> <p>Side panel: Sheet steel, 1.2 mm</p> <p>482.6 mm (19") mounting angles: Sheet steel, 2 mm</p> <p>Side panel: Sheet steel, 1.2 mm</p>
Surface finish	<p>Enclosure frame: Dipcoat-primed</p> <p>Enclosure panels: Dipcoat-primed, powder-coated</p>
General colour	RAL 7035
Colour	RAL 7035
Supply includes	<p>Enclosure with glazed front door and rear door</p> <p>Enclosure frame with 482.6 mm (19") mounting angles, front and rear</p> <p>Side panels</p> <p>Base/plinth system VX, 100 mm, vented</p> <p>Brush strip</p> <p>19" combination rail</p> <p>50 multi-tooth screws M5, cage nuts M5, conductive (supplied loose)</p> <p>Cable shunting rings (supplied loose)</p> <p>Assembly parts</p> <p>Screw-fastened roof plate with concealed cable entry on both sides across the entire enclosure depth plus a central, concealed cut-out for easy integration of a fan module.</p>
Dimensions	<p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 800 mm</p>
Units	42 U

Features

Distance between levels as delivered	445 mm
Design	Pre-configured with side panels
Rear door design	Sheet steel door, one-piece, solid
Front door design	Glazed door, one-piece With 3 mm single-pane safety glass Door opening angle when baying: max. 105°
Load capacity	5000 N
Load capacity (static)	500 kg
Protection category to IEC 60 529	IP 20
Note	To install a fan module, brush strips for fitting to the cable shunting openings are necessary if these are being used, or if the covers have been removed. Brush strips to conceal the cable entry are available separately and may be conveniently ordered from our accessory range.
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	132,5 kg
Gross weight	142,5 kg
Customs tariff number	94032080
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207
Product description	TX CableNet, with glazed door, with roof plate, side panels, 19" mounting angles, pre-assembled, WxHxD: 800x2000x800 mm, RAL 7035

Approvals

Approvals

Approvals

UL + C-UL (listed)

Tender text

IT rack, installation height 42 U, glazed door at the front, One-piece closed sheet steel door at the rear. Article number 7888.898

Frame structure:

IT rack, consisting of a torsion-resistant, welded, symmetrical frame made of rolled and 16-folded vertical profiles, connected to a horizontal frame below and horizontal cross profiles, with screwed roof plate at the top. All frame profiles, with integrated system perforation in a 25 mm hole grid, enable convenient interior design by simply hanging and securing the installation components. All profile edges are rounded. The vertical frame profiles each have two in depth and width staggered mounting levels, which can be individually adjusted for flexible fastening of the components. The baying of the cabinets is possible at the front, back and side. Load capacity: up to 500 kg.

Floor:

Equipped with a 100mm high ventilated plinth.

The side panels of the plinth are pre-assembled to the bottom of the frame, while the ventilated sections, along with other accessories, are located inside. The accessories are attached loosely to the rear rail.

Front and back door:

Transparent door at the front, with 3 mm toughened safety glass.

Steel sheet door at the rear, one-piece, closed.

Front and rear doors each double hinged, with designer handle and 2-point bar lock, Safety lock 3524 E, replaceable with AX comfort handle
Optional integration of a semi-cylinder. Swapping door hinge side possible, door opening angle 135° when installed individually, 105° in array. Door hinges with captive hinge pins.

Roof sheet:

Sheet steel roof, one-piece, closed, screwed, prepared for cable routing on the side, prepared in the middle for fan installation with up to 6 fan units. Roof plate can be rotated for cable routing at the front and rear. To support passive ventilation the roof sheet can optionally be raised using spacers.

Mounting levels:

Cabinet pre-assembled with two 482.6 mm (19") mounting levels, front and rear. The total static load capacity of both assembly levels is 500 kg.

Mounting levels consisting of universal profile rails, front and rear, variable in width and depth, in 15 mm dimensions, on depth struts at the

top and bottom

in the cabinet frame, screwed.

The 19" mounting levels can be positioned both symmetrical and asymmetrical with lateral offset, positioned in the housing.

Profile rails at the front and back, included additional hole pattern according to standard EIA 310 E. All height units marked on the profile rails and numbered bidirectionally.

Unit marking on both mounting levels for simplified assembly of the installation components can be read from the front outside and the back inside.

Profile rails at the front prepared for tool-free mounting of cable management aids for organizing structured cabling within highest packing density. Profile rails at the rear prepared to accommodate a Power Distribution Unit (PDU) on both sides with the 1U form factor, without consumption of installation volume due to the special space-saving lateral installation between the mounting level and the side wall within

Zero U Space.

Side walls:

One-piece screwed side walls mounted on the cabinet.

Material:

Cabinet frame, roof: sheet steel 1.5 mm

Roof cutouts: 1.2mm

Rear door: sheet steel 1.2 mm

Front door: sheet steel 1.2 mm, safety glass 3.0 mm

19" profile rails: sheet steel 2.0 mm

Surface:

Flat parts, doors dip-primed, powder-coated in RAL 7035

Interior installation dip primed in RAL 9005

Cabinet frame dip primed in RAL 7035

Approvals:

CE declaration of conformity

RoHS 3

Dimensions (WHD): 800x2000x800 mm

Item number: 7888.898

Manufacturer: Rittal GmbH & Co. KG