


# Rittal – The System.

Faster – better – everywhere.



## DK 7979.615 PDU local metered

State: 04.06.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7979.615 - PDU local metered

High-end power distribution with local measurement of consumption data. Ideally suited for use in modern server racks and colocation data centres.

## Features

Model No.	DK 7979.615
Design	Blue
Product description	The PDU with local power measurement is equipped with one display per phase (two displays in total) and supports superior phase loads in the colocation data centre.
Benefits	Integral measurement of current (A); active power (kW); voltage (V); frequency (Hz); power (kWh) and phase angle (°) Measurement accuracy of $\pm 2\%$
Technical specifications	Error-tolerant PDU power supply redundant across all phases Connection cable, with connector, 3 m, H05VV-F3G4 mm <sup>2</sup> Voltage V, current A, frequency Hz LCD display
Function principle	Measurement per phase or infeed
Material	Aluminium, spray-finished, blue, similar to RAL 5010 Cover: Plastic PA 6 GF30, black, similar to RAL 9005
Supply includes	PDU with local measurement, 32 A, 1-phase, blue 2 angle brackets
Measurement functions, description	Measurement per phase or infeed
Dimensions	Width: 44 mm Depth: 47 mm Length: 1,308 mm
No. of sockets and type	24 x C13 / 6 x C19 IEC/EN/60320/C13 IEC/EN/60320/C19

# Features

Sockets	24 x C 13 6 x C 19 2-pole with protective contact, black
Rated operating voltage	230 V, 50 Hz/60 Hz
Rated current (max.)	32 A
Power consumption	7,4 kW
Infeeds	Qty.: 1 Phases per infeed: 1~
Length of connection cable	3 m
Type of electrical connection	CEE
Directives	EMC directive 2014/30/EU Low Voltage Directive 2014/35/EU
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	5...95 %
Storage temperature range	-5 °C...60 °C
To fit	Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: TX Colocation Rack: ≥ 1,800 mm
Packs of	1 pc(s).
Net weight	3,5 kg
Gross weight	3,5 kg
Customs tariff number	85366990
ETIM 9	EC002762
ETIM 8	EC002762
ECLASS 8.0	27142606
Product description	PDU with local power measurement, blue version, 24x C13, 6x C19, 2-pole with earthing contact, black, WxHxD: 44x1308x47 mm

# Approvals

---

Approvals

Cyber Security Certificate

# Tender text

Rittal PDU local metered Model No.: DK 7979.615

PDU local metered 32A/1P CEE 24xC13 / 6xC19

Compact power distributor for deployment in IT server and network enclosures.

Robust aluminum housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19.

A fixed-mounted connection cable with CEE connector makes the PDU available for immediate deployment.

The PDU metered has extensive measurement functions for the current and power monitoring.

The integral TFT colour display enables quick access to the electrical consumption data.

Technical specifications PDU local metered:

Input voltage range (L1/N/PE): 230 VAC, 50-60Hz

input current: 32A

No. of phases: 1

Number of slots type IEC 60320/C13 (total): 24

Number of slots type IEC 60320/C13  
(per fuse): 12

Number of slots type IEC 60320/C19 (total): 6

Number of slots type IEC 60320/C19  
(per fuse): 3

No. of circuit breakers: 2

Hydraulic-magnetic protective circuit-breaker: 16 A

Connector PDU input:

EN 60309 / CEE

Length of connection cable: 3m

Connection cable type: H05VV-F

No. of wires: 3

Cable cross-section: 4 mm<sup>2</sup>

PDU housing width: 44mm

PDU housing depth: 47mm

PDU housing height: 1308mm

PDU material: Aluminum, painted blue RAL 5010

PDU mounting adaptor included

Measurement functions: Measurement per fuse:

Values recorded (per fuse):

Voltage (V), current (A), frequency (Hz), Power factor(>,<)>  
active energy (kWh), Active power(kW)  
Voltage measuring range: 90V - 255V  
Voltage resolution 0.1V  
Current measuring range 0 - 16A/32A  
Current resolution 0.1A  
Measuring accuracy typ.  $\pm 2\%$   
Conformity: CE  
Protection category: IP 20  
Storage temperature: -20 °C to +60 °C  
Ambient temperature: +5°C to +45°C  
Ambient humidity <80% rel. humidity, non-condensing  
Type: Rittal PDU local metered, Model No.: DK 7979.615