

Rittal – The System.

Faster – better – everywhere.



VX 7993.919

Bayed enclosure system VX25

State: 06.08.2025 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 7993.919 - Bayed enclosure system VX25 Daimler

Integra standard

Daimler Integra enclosure with rear door or with plug-in rear panel, without mounting plate, for installing a wiring system.

Features

Model No.	VX 7993.919
Design	With rear panel
Product description	Stable symmetrical extrusion frame, consisting of rolled hollow sections with all-round 25 mm DIN pitch pattern of holes at all section levels, horizontal and vertical. Extrusions with two mounting levels for space-saving interior installation, identical punched sections for mounting on the vertical and horizontal frame sections, mounting levels accessible from outside, integral reinforcements for stable fixing to the floor. Simple and stable baying to all sides with a minimum of parts. 3-part gland plate, removable and exchangeable, fitted. Doors with foamed-in seal and locking rod, with a floor clearance of 25 mm at the bottom.
Material	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm
Surface finish	Enclosure frame: Dipcoat-primed Enclosure panels: Dipcoat-primed, powder-coated Gland plates: Zinc-plated Tubular door frame, zinc-plated
Colour	RAL 7035

Features

Supply includes	<p>Enclosure frame</p> <p>Door(s)</p> <p>Roof plate screw-fastened with four eyebolts 2568.000</p> <p>Gland plates</p> <p>without mounting plate</p> <p>Double front door with square tubular door frame, with fitted 180° hinges 8618.330 and fitted double-bit lock insert 8618.306.</p> <p>2 plug-in rear panels with vertical cross-member including potential equalisation, latched with 6 cams each (3 on the left, 3 on the right), including zinc-plated locking catch and double-bit lock insert</p> <p>Adjacent door(s) additionally latched with swivel handle at the top and bottom.</p> <p>Bracket, zinc-plated, conductively screw-fastened to the vertical section, as counterpart to the cam</p> <p>2 plug-in brackets right and left, screw-fastened to the bottom horizontal section</p> <p>Contact bracket screw-fastened to the bottom horizontal section</p> <p>Depending on the rear panel, one earth strap 400 mm long, 4 mm², one end with ring terminal, one end with eyebolt (supplied loose)</p> <p>Potential equalisation of the roof, side panels and gland plates is achieved automatically during assembly via contact elements</p> <p>Potential equalisation of the plug-in rear walls is achieved with forced contact</p>
Dimensions	<p>Width: 1,200 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 500 mm</p>
Protection category to IEC 60 529	IP 55
Number of doors	2
Packs of	1 pc(s).
Net weight	127.23
Gross weight	137.6