

**Rittal – The System.**

Faster – better – everywhere.



**TS 8601.015**

**Base/plinth trim panels, side, 100 mm**

State: 07.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8601.015 - Base/plinth trim panels, side, 100 mm for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used. Base/plinth trims may be installed rotated through 90° in order to stabilise bayed base/plinth components.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | TS 8601.015  |
| Product description   | For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trim panels may be used.   |
| Material              | Sheet steel  |
| Surface finish        | Spray-finished   |
| Colour                | RAL 7035   |
| Supply includes       | 2 base/plinth trim panels<br>Assembly parts  |
| Assembly instruction  | Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose |
| Dimensions            | Height: 100 mm   |
| To fit                | Enclosure type: TS: = 1,000 mm<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT              |
| Packs of              | 2 pc(s).   |
| Net weight            | 3,442 kg   |
| Customs tariff number | 94039910   |
| ECLASS 8.0            | 27182003   |

# Features

---

Product description

TS Trim panel, sides, H: 100 mm, for W: 1000 mm, RAL 7035, sheet steel

## Tender text

Base/plinth side trim, for TS, enclosure depth 1000 mm

Base/plinth trim for finishing off the side of the base/plinth in connection with TS base/plinth components. To stabilise bayed base/plinths and for easy cable routing between the enclosures.

May be installed rotated through 90°.

For this a base/plinth baying bracket TS 8601.100 is also required.

Material: Sheet steel, spray-finished

Colour: RAL 7035

Trim height: 100 mm

For enclosure depth: 1000 mm