

**Rittal – The System.**

Faster – better – everywhere.



**VX 8660.120**

**Levelling component**

State: 06.02.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 8660.120 - Levelling component for base/plinth system VX, sheet steel

For retrospective levelling on uneven floors at the installation site up to a maximum of 15 mm.  
Installed through the base/plinth corner piece.



## Features

Model No.	VX 8660.120
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Load capacity	Max. admissible load: 2500 N per levelling component
Note	For use in combinations of VX, VX IT, VX SE, TX, TS, TS IT, PC, IW, TP with the base/plinth system VX Check the load capacity of the floor.
Dimensions	Height: 100 mm
Weight/pack	0,612 kg
Packs of	4 pc(s).
To fit	for base/plinth system VX, sheet steel
Net weight	0.56
Gross weight	0.611
Customs tariff number	73181900
EAN	4028177984813
ETIM 9	EC004043

# Features

---

ETIM 8 EC000721

---

ECLASS 8.0 27182003