


Rittal – The System.

Faster – better – everywhere.



KEL 9201.600 Ex enclosures

State: 24.05.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9201.600 - Ex enclosures Plastic, empty enclosure with hinged door

Ex enclosure with hinged door, plastic

Features

Model No.	KEL 9201.600
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material	Fibre-glass-reinforced unsaturated polyester, surface resistance: < 10 ¹⁰ Ω Door: Fibreglass-reinforced unsaturated polyester, surface resistance: < 10 ¹⁰ Ω, all-round foamed-in silicone seal Mounting plate: Sheet steel, zinc-plated
Colour	RAL 9011
Supply includes	Enclosure Door Mounting plate
Dimensions	Width: 200 mm Height: 300 mm Depth: 150 mm
Dimensions mounting plate (W x H)	145 mm x 250 mm
Certificate IEC EX PTB 10.0011U	Yes
Certificate PTB 03 ATEX 1011U	Yes
Basic material	Plastic

Features

Lock	Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit
IP protection category to IEC 60529	IP 66
Packs of	1 pc(s).
Net weight	3.11
Gross weight	3.31
Customs tariff number	94037000
EAN	4028177138216
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals	ATEX
Certificates	Protection category
Explanations	Manufacturer's declaration