

# Rittal – The System.

Faster – better – everywhere.



## KEL 9305.000 Ex enclosures

State: 03.07.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9305.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel



## Features

Model No.	KEL 9305.000
Design	Ex enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Enclosure Cover
Dimensions	Width: 400 mm Height: 200 mm Depth: 120 mm
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)

# Features

---

IP protection category to IEC 60529	IP 66
Packs of	1 pc(s).
Net weight	3,4 kg
Gross weight	3,6 kg
Customs tariff number	94032080
ETIM 9	EC002503
ECLASS 8.0	27180502
Product description	KEL Ex enclosure, WHD: 400x200x120 mm, Stainless steel 1.4301, without mounting plate, Empty enclosure with screw-fastened cover

# Approvals

---

Approvals	ATEX ATEX QA CQC-CCC IECEX IECEX QAR
Explanations	Attestation of Conformity