Rittal – The System.

Faster – better – everywhere.



SV 9340.270 **OM** supports

State: 18.11.2025 (Source: rittal.com/bg-bg)



SV 9340.270 - OM supports without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.270
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
For bar systems with centre-to- centre spacing	60 mm
Support rail type	Support frame, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 55 mm Height: 272 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	55 mm x 237 mm
Packs of	1 pc(s).
Net weight	0.25
Gross weight	0.258
Customs tariff number	85369095
EAN	4028177502475
ETIM 9	EC001166
ECLASS 8.0	27400607

© Rittal 2025

Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

Tender text

OM support (without contact system)

OM support without contact system (3-pole)

for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications
Construction width: 55 mm

Length: 272 mm

Support frame: 55 x 237 mm Support frame support: yes

PinBlock: -Support rail: 1

System:

Rittal RiLine60

© Rittal 2025