## Rittal – The System.

Faster – better – everywhere.





# RX 9360.000 RiLineX baying set

State: 02.11.2025 (Source: rittal.com/bg-bg)



## RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.

#### **Features**

Model No.	RX 9360.000
Benefits	Time savings thanks to fully digital product data
	Reduced assembly time thanks to pre-assembled complete board
	Tested short-circuit resistance up to 65 kA
	Suitable for applications up to 1000 V AC and up to 1500 V DC
	Contact hazard protection up to IP 2XB, upgradable to IP 3X
	Tested and certified to IEC and UL
	Simple extension and baying
Material	Upper part: Sheet steel, zinc-plated
	Contact plate: E-Cu, tin-plated
	Front cover: Polyamide (PA 6)
	Fire protection corresponding to UL 94
Colour	RAL 35745
Supply includes	3 busbar connectors
	1 front cover
	1 insulating plate
IP protection category to IEC 60 529	IP 2XB
Standards	IEC 61 439-1/-2
	UL 508
Rated current max.	780 A
Rated current (UL)	780 A
Electrical ratings UL (SCCR)	52.5 kA - 600 V, RMS
	100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7
	100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7
	100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7
	65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7

© Rittal 2025

### Features

Rated impulse withstand voltage	12 kV
Uimp	
Rated voltage	1000 V AC
	1500 V DC
	600 V AC (UL)
	600 V DC (UL)
Rated insulation voltage	1000 V AC
	1500 V DC
Rated impulse withstand current	103 kA
	115,5 kA
Rated short-term withstand	45 kA/200 ms
current/t	52.5 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	5060 Hz
Ambient humidity (non-	1090 %
condensing)	
To fit busbars	30 x 5/10
Operating temperature range	-5 °C55 °C
Dimensions	Width: 153 mm
	Height: 240 mm
	Depth: 77 mm
Packs of	1 pc(s).
Net weight	1.88
Gross weight	1.924
Copper weight (kg per piece)	0.297
Customs tariff number	85369010
EAN	4028177997431
ETIM 9	EC002270

© Rittal 2025 3

## Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025