

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.705

## RiLineX component support

State: 09.09.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.705 - RiLineX component support without contact system

RiLineX component support in width 45 mm for RiLineX and 60 mm busbar system platforms, without contact system. Ideal for securing wider equipment onto the board.



## Features

|   |   |
|---|---|
| Model No.                                     | RX 9360.705   |
| Design  | without contact system  |
| Benefits                                      | For mounting equipment for top hat rail installation, e.g. motor starter<br>Simple clip locking for support rails<br>Optional anti-slip guard<br>Coordinated accessories reduce the number of different items required<br>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) |
| Material                                      | Polyamide (PA 6)<br>Fire protection corresponding to UL 94  |
| Colour  | RAL 9005  |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Dimensions                                    | Width: 45 mm<br>Height: 240 mm<br>Depth: 37 mm  |
| To fit busbars                                | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |

## Features

|                       |  |
|-----------------------|--|
| To fit busbar system  | RiLineX<br>RiLine60                        |
| Number of poles       | 3-pole                                     |
| Support rails Qty     | 1  |
| Rated voltage         | 690 V AC<br>600 V AC (UL)<br>600 V DC (UL) |
| Packs of              | 4 pc(s).                                   |
| Net weight            | 1.16                                       |
| Gross weight          | 1.2  |
| Customs tariff number | 85369095                                   |
| EAN                   | 4028177997059                              |
| ETIM 9                | EC001531                                   |

## Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |