

Rittal – The System.

Faster – better – everywhere.



SV 9340.760 OM adaptors

State: 09.07.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.760 - OM adaptors with connection cables

Features

Model No.	SV 9340.760
Design	With connection cable
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Connection cables (AWG)	AWG 12
Rated current max.	16 A
Rated operating voltage	690 V, 3~
Note	The technical data may vary for UL applications
Electrical ratings UL (SCCR)	30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7 50 kA - 600 V, Fuse Class K5 max. 35 A, JDDZ/7 65 kA - 600 V, Fuse Class J max. 30 A, JDDZ/7 65 kA - 600 V, Fuse Class K5 max. 30 A, JDDZ/7 50 kA - 480 V, Combination Motor Controller max. 27 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 32 A, NKJH/7
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	165 mm
Support rail type	Support frame, 1 x TS 45D, PinBlock
Number of poles	3-pole
PinBlock	Yes
Support frame support	Yes
Dimensions	Width: 45 mm Height: 272 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	Height: 5, 10 mm

Features

Support frame (W x H)	45 mm x 237 mm
Approvals	UL
Packs of	1 pc(s).
Net weight	0,2 kg
Gross weight	0,314 kg
Copper weight (kg per piece)	0,038
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 16 A, 690 V, 3-pole, connection cable AWG 12, WH: 45x272 mm, support frame, PinBlock, support rail TS 45D

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
-----------	---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---