

Rittal – The System.

Faster – better – everywhere.



RX 9360.798

RiLineX component adaptor

State: 04.09.2025 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.798 - RiLineX component adaptor

RiLineX component adaptor (80 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar system platforms. With integral threaded inserts. Sample for standard commercially available circuit-breakers.



Features

Model No.	RX 9360.798
Design	With connection cable
Benefits	For mounting equipment for top hat rail installation, e.g. motor starter Pre-assembled connection cable Simple clip locking for support rails Optional anti-slip guard Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Simple assembly Coordinated accessories reduce the number of different items required
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 4
Rated current max.	80 A
Cable outlet	Top
For bar systems with centre-to-centre spacing	60 mm

Features

Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 72 mm Height: 240 mm Depth: 37 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	1 pc(s).
Net weight	0.7
Gross weight	0.702
Copper weight (kg per piece)	0.246
Customs tariff number	85369095
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity