

Rittal – The System.

Faster – better – everywhere.



SV 9343.250

NH fuse-switch disconnecter

State: 14.05.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.250 - NH fuse-switch disconnecter with electromechanical fuse monitoring

Features

| | |
|---|---|
| Model No. | SV 9343.250 |
| Design | For 60 mm busbar systems |
| Material | Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | Chassis: RAL 7035 Cover: RAL 7035/7001 |
| Clamping area for laminated copper bars | Clamping area width: 50 mm Clamping area height: 10 mm |
| For bar systems with centre-to-centre spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M10 |
| Rated operating current max. | 400 A |
| Rated operating voltage | 690 V, 3~ |
| For NH size | 2 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |
| Dimensions | Width: 210 mm Height: 298 mm |
| Connection of round conductors | 10 - 240 mm ² |
| To fit busbars | Height: 5, 10 mm |
| Number of poles | 3-pole |
| Round conductor cross-section | 10 - 240 mm ² |

Features

| | |
|------------------------------|---|
| Packs of | 1 pc(s). |
| Net weight | 3,66 kg |
| Gross weight | 3,71 kg |
| Copper weight (kg per piece) | 1 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC000249 |
| ECLASS 8.0 | 27371401 |
| Product description | SV NH fuse-switch disconnecter, size 2, 400 A, 690 V, 3-pole, screw M10, with electromechanical fuse monitoring |

Approvals

| | |
|--------------|---|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity Declaration of conformity UK |