

Rittal – The System.

Faster – better – everywhere.



RX 9360.600

RiLineX CB component adaptor

State: 07.02.2026 (Source: rittal.com/bg-bg)

RX 9360.600 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

Features

Model No.	RX 9360.600
Design	universal
Benefits	<p>Direct mounting of moulded-case circuit-breakers (MCCBs) on the board</p> <p>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm</p> <p>Fast, simple pre-assembly of standard market switch types outside of the enclosure</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
Colour	<p>RAL 9005</p> <p>RAL 35745</p>
Supply includes	3 connection space covers
IP protection category to IEC 60 529	IP 2XB
Rated impulse withstand voltage U _{imp}	12 kV
Rated voltage	<p>690 V AC</p> <p>690 V DC</p> <p>600 V AC (UL)</p>
Rated insulation voltage	1000 V
Overvoltage category	4
Contamination level	3

Features

Clamping area for laminated copper bars (W x H)	9 x 6 mm
Number of poles	3-pole
Cable outlet	Bottom
Type of electrical connection	Box terminal
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 81.9 mm Height: 251.4 mm Depth: 50.8 mm
Packs of	1 pc(s).
Net weight	0.92
Gross weight	1.22
Copper weight (kg per piece)	0.375
Customs tariff number	85369095
EAN	4028177997103
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity