

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.730

## RiLineX component adaptor

State: 07.07.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.730 - RiLineX component adaptor

RiLineX component adaptor (40 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.



## Features

Model No.	RX 9360.730
Design	With connection cable
Benefits	<ul style="list-style-type: none"><li>For mounting equipment for top hat rail installation, e.g. motor starter</li><li>Pre-assembled connection cable</li><li>Simple clip locking for support rails</li><li>Optional anti-slip guard</li><li>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</li><li>Simple assembly</li><li>Coordinated accessories reduce the number of different items required</li></ul>
Material	<ul style="list-style-type: none"><li>Polyamide (PA 6)</li><li>Fire protection corresponding to UL 94</li></ul>
Colour	<ul style="list-style-type: none"><li>RAL 9005</li><li>RAL 35745</li></ul>
Connection cables (AWG)	AWG 10
Rated current (max.)	40 A

# Features

Rated current of round conductor	40 A
Rated current of round conductor (UL)	40 A
Cable outlet	Bottom
For bar systems with centre-to-centre spacing	60 mm
Length of connection cable	160 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Rated impulse withstand voltage U <sub>imp</sub>	8 kV
Rated insulation voltage U <sub>i</sub>	1000 V
IP protection category to IEC 60529	IP 2XB
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C

# Features

---

Ambient humidity (non-condensing)	10...90 %
Fire load	3,419 MJ/m <sup>2</sup>
Packs of	4 pc(s).
Net weight	1,42 kg
Gross weight	1,45 kg
Copper weight (kg per piece)	0,088
PCF per pack (cradle-to-gate)	9.34
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RiLineX component adaptor (40 A, 3-pole, including connection cables) in width 45 mm for RiLineX and other 60 mm busbar system platforms. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration

# Tender text

RiLineX component adaptor with mounting rail

Device adapters for mounting protective and switching devices for 60 mm busbar systems.

The device is mounted on a pre-assembled, adjustable mounting rail.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 40 A

Connection: 6 mm<sup>2</sup>

Cable outlet: top

Dimensions: 45 mm x 240 mm x 37 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360730