


# Rittal – The System.

Faster – better – everywhere.



## SV 9635.400 Motor controller

State: 10.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9635.400 - Motor controller 3-pole

For controlling motors as direct or reversing starters with integral over-ride protection

## Features

Model No.	SV 9635.400
Function principle	For controlling motors as direct or reversing starters with integral over-ride protection The hybrid technology used facilitates frequent switching by semi-conductors with zero wear During operation, mechanical contacts ensure a low heat loss Space-saving configuration thanks to the minimal build width
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Heat loss max.	2,8 W
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz
Rated current max.	0,6 A
Note	The technical data may vary for UL applications
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm
Connection of round conductors	0.14 - 2.5 mm <sup>2</sup>
Adjustable current monitoring	0.075 - 0.6 A
Packs of	1 pc(s).
Net weight	0,38 kg
Gross weight	0,389 kg
Customs tariff number	85371091
ETIM 9	EC002572
ECLASS 8.0	27370804

# Features

---

Product description	SV Motor controller, 0,6 A, 500 V, 50/60 Hz, 3-pole, round conductor connection 0,14-2,5 mm <sup>2</sup> , WH: 22,5x160 mm
---------------------	--

# Approvals

---

Approvals	UL + C-UL (listed)
-----------	--------------------

---

Explanations	Declaration of conformity
--------------	---------------------------