

Rittal – The System.

Faster – better – everywhere.



RX 9363.005

RiLineX NH fuse-switch disconnecter

State: 05.04.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9363.005 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Includes electronic fuse monitoring.



Features

| | |
|-----------------------------|---|
| Model No. | RX 9363.005 |
| Design | For mounting plate assembly |
| Benefits | Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | RAL 9005 RAL 35745 |
| Supply includes | Connectors for electronic fuse monitoring |
| for mounting plate assembly | Yes |
| Cable outlet | Top/bottom |

Features

| | |
|--------------------------------------|--|
| Type of electrical connection | Screw M8 |
| Fuse inserts | NH 00 NH 000 |
| Rated insulation voltage U_i | 1000 kV |
| Rated operating voltage | 690 V AC |
| For NH size | 00 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |
| Dimensions | Width: 106 mm Height: 228.9 mm Depth: 86.1 mm |
| Operating temperature range | -5 °C...35 °C |
| Storage temperature range | -25 °C...70 °C |
| Number of poles | 3-pole |
| Utilisation category | AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A) |
| Contamination level | 3 |
| with electronic fuse monitoring | Yes |
| IP protection category to IEC 60 529 | IP 2XB |
| Fire load | 13,24 MJ/m ² |
| Heat loss max. | 16 W |
| Heat loss per fuse insert (max.) | 12 W |
| Packs of | 1 pc(s). |
| Net weight | 0,82 kg |
| Gross weight | 0,917 kg |
| Copper weight (kg per piece) | 0,18 |
| Customs tariff number | 85369095 |

Features

ETIM 9

EC001040

Product description

RiLineX NH fuse-switch disconnecter in size 00 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Includes electronic fuse monitoring.

Approvals

Explanations

Declaration of conformity
PCF-declaration

Tender text

RiLineX NH fuse-switch disconnecter (size 00 mit ESÜ)

NH fuse-switch disconnecter for mounting on mounting plate.

Other properties include sealability,

Voltage test via separate openings,

Parking position for the cover and lockability with padlocks in the open position (service case).

Rated voltage 690 V AC.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm

Busbar dimensions: 5/10 mm

Rated current: 160 A

Type of electrical connection: Screw M8

Cable outlet: top/bottom

Dimensions: 106 mm x 230 mm x 105 mm (BxHxT)

Feature: Electronic fuse monitoring

Manufacturer: Rittal GmbH & Co. KG

Type: 9363005