

Rittal – The System.

Faster – better – everywhere.



SV 9393.558 Current transformer

State: 25.06.2026 (Source: rittal.com/bg-bg)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.558 - Current transformer

Features

| | |
|-----------------------------------|---|
| Model No. | SV 9393.558 |
| Design | Output voltage 333 mV |
| Material | Polyamide Fire protection corresponding to UL 94 |
| Colour | RAL 9005 |
| Supply includes | 2 plug-in feet 2 insulating caps 1 primary bar clamp 2 grub screws |
| To fit busbars | 60 x 15 2 x 50 x 10 |
| Primary current | 630 A |
| Standards | EN 61869-1/ 2 EN 42600 VDE 0100 EN 50274 / VDE 0660-514 DGUV regulation 3 |
| Dimensions | Width: 85 mm Height: 108 mm Depth: 30 mm |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Ambient humidity (non-condensing) | 10...90 % |
| Fundamental frequency | 50...60 Hz |
| Accuracy Class | 0,5 |
| Insulation material (class) | F |

Features

| | |
|-----------------------|-------------------------------------|
| Packs of | 1 pc(s). |
| Net weight | 0,295 kg |
| Gross weight | 0,309 kg |
| Customs tariff number | 85043129 |
| ETIM 9 | EC002048 |
| Product description | SV Current transformer 630 A, 52 mm |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|
